

Examples of uses



- ◆ The load bearing in use of both of arms is 10kg for DIT-250, and 16kg for DIT-350.
- lacklost The load bearing includes the hanger pipe weight itself. Hanger pipes 32 ϕ or less are separately needed.

The arms go down slowly with damper mechanism, it keeps safe and secure λ



Easy to fold up the arms even at heights.







You can stote the arms without a stepladder regardless of its mouting height.

Easy mounting steps














- You can attach them everywhere on plasterboards without wood backing.
- Nails will be hammered into the wall, and fixed on the wall tightly.




Indoor Laundry Holder "DRYit"


material: [body] SUS Stainless Steel, Alminium, ABS resin [decorative cover] ABS resin

item	color	length	carton
DIT-250	white	250mm	10pcs
DIT-350	white	350mm	10pcs











website: www.shimizu-net.co.jp email: info@shimizu-net.co.jp

Shimizu Website